

Infrared Attendance Pendant (push for attendance)

Part No. **QT432A**



Overview

- Allows nursing or security staff entering rooms during night shifts, etc., to log their attendance.
- Upon activation, the infrared call point or ceiling receiver that picks up the Attendance call flashes to confirm the call has been registered.
- All Attendance calls are logged together with the pendant's ID in Quantec's onboard datalogger or optional Surveyor Data Management Software.
- 10m line-of-sight IR transmitting range.
- Powered by a user-replaceable 12V alkaline battery.
- Allows managers to monitor which staff are performing their duties and to reassure users, relative and regulatory authorities that patients and/or buildings are being checked periodically.
- Must be used in conjunction with additional Quantec infrared devices.



More Information

Technical Specifications

Compatibility	Compatible with C-TEC's Quantec call systems.
Type	Infrared/Radio.
Coverage	10m line-of-sight infrared coverage (940nm modulated @ 38 Khz); 60m typical radio coverage dependent on environmental factors (RF868.3 MHz).
Max battery size and type	12 Volt Type A23/23A (8LR50) alkaline (non-rechargeable). User replaceable.



Indicators	Confidence LED/battery status indicator.
Controls	1 x activation button (triggers an Attendance call).
Product dimensions (mm)	47 W x 83 H x 16 D mm.
Construction & finish	TBC.
IP Rating	IP41.
Weight	30g.
Operating conditions/temperature	-5°C to +40°C. Max. relative humidity 95% non-condensing.



T 01942 322744 E sales@c-tec.co.uk
F 01942 829867 W www.c-tec.com



C-TEC, Challenge Way, Martland Park, Wigan, WN5 0LD United Kingdom